

HEIDENHAIN



Product Information

ECI 4090S

Absolute Rotary Encoder with 90 mm Hollow Shaft and DRIVE-CLiQ Interface for Safety-Related Applications

Firmware 15





ECI 4090S


Rotary encoder for absolute position values with safe singleturn information


- Robust inductive scanning principle
- Hollow through shaft (Ø 90 mm)
- . Consists of a scanning unit and scale drum











- M1 = Measuring point for operating temperature on housing
- M2 = Measuring point for vibration on housing
- 1 = Position of zero point ±5°
- 2 = Maximum permissible axial deviation between the shaft surface and flange surface;
- compensation of mounting tolerances and thermal expansion; dynamic motion permitted over entire range
- 3 = Use screws with material bonding anti-rotation lock: ISO 4762 M4 x 25 8.8 MKL as per DIN 267-27 (not included in delivery, ID 202264-88); tightening torque: 2.2 Nm ±0.13 Nm
- 4 = Space required when encoder cover is closed
- 5 = Space required for opening the encoder cover
- 6 = Total runout of mating shaft
- 7 = Coaxiality of stator mating surface
- 8 = Bearing surface of rotor
- 9 = Bearing surface of stator
- 10 = Chamfer at start of thread is mandatory for material bonding anti-rotation lock
- 11 = Direction of shaft rotation for ascending position values
- 12 = This area of the mating surface does not need to be fully covered by the scanning unit

Tolerancing ISO 8015 ISO 2768:1989-mH ≤ 6 mm: ±0.2 mm

Specifications	ECI 4090 S singleturn	
Functional safety for applications with up to	As a single-encoder system for monitoring functions and closed-loop functions SIL 2 as per EN 61508 (further basis for testing: IEC 61800-5-3) Category 3, PL d as per EN ISO 13849-1:2015 Safe in the singleturn range	
PFH ¹⁾	$S/L \ 2: \le 27 \cdot 10^{-9}$ (probability of dangerous failure per hour)	
Safe position ²⁾	Encoder: $\pm 0.44^{\circ}$ (safety-related measuring step: SM = 0.176°) Fault exclusion for the loosening of AE scanning unit and TTR scale drum, designed for acceleration of AE : $\leq 400 \text{ m/s}^2$; of TTR : $\leq 600 \text{ m/s}^2$	
Interface	DRIVE-CLiQ	
Ordering designation	DQ01	
Firmware	01.32.27.15	
SINAMICS, SIMOTION ³⁾	≥ V4.6 HF3	
SINUMERIK with safety ³⁾	≥ V4.7 SP1 HF1	
SINUMERIK without safety ³⁾	≥ V4.5 SP2 HF4	
Position values per revolution	1048576 (20 bits)	
Calculation time TIME_MAX_ ACTVAL ⁴⁾	≤ 11 µs	
System accuracy	±25"	
Electrical connection	15-pin PCB connector (with connection for external temperature sensor ⁵⁾)	
Cable length ⁶⁾	≤ 40 m (see description in the Interfaces of HEIDENHAIN Encoders brochure)	
Supply voltage	DC 24 V (10 V to 28.8 V); up to 36 V possible without limiting functional safety	
Power consumption ⁷⁾ (max.)	At 10 V: ≤ 1100 mW; at 28.8 V: ≤ 1250 mW	
Current consumption (typical)	At 24 V: 40 mA (without load)	
Shaft	Hollow through shaft (Ø 90 mm)	
Shaft speed	≤ 6000 rpm	
Moment of inertia of rotor	4.26 · 10 ⁻⁴ kgm ² (without screws)	
Angular acceleration of rotor	$\leq 2 \cdot 10^4 \text{rad/s}^2$	
Axial motion of measured shaft	≤ ±1.5 mm	

For use at an elevation of ≤ 1000 m above sea level

2 3 Product Information ECI 4090 S 11/2024 Product Information ECI 4090S 11/2024

²⁾ Further tolerances may arise in the downstream electronics after position value comparison (contact mfr. of the downstream electronics)

³⁾ Information from Siemens as per the document "Certified encoders with DRIVE-CLiQ Dependencies on SIMOTION / SINUMERIK and SINAMICS Hardware and Software versions" (version: 04/2019)

⁴⁾ The calculation time TIME_MAX_ACTVAL specifies the time after which a data transfer from the encoder to the control can start within the current-regulator clock time

⁵⁾ See *Temperature measurement in motors* in the *Encoders for Servo Drives* brochure


 $^{^{6)}}$ With an output cable length (inside the motor) \leq 1 m


⁷⁾ See General electrical information in the Interfaces of HEIDENHAIN Encoders brochure

Specifications	ECI 4090 S singleturn		
Vibration 55 Hz to 2000 Hz ⁸⁾ Shock 6 ms	AE scanning unit: \leq 400 m/s ² ; TTR scale drum: \leq 600 m/s ² (EN60068-2-6) \leq 2000 m/s ² (EN 60068-2-27)		
Operating temperature	-40 °C to 100 °C (at the measuring point and on the entire scale drum)		
Trigger threshold for exceeded temperature error message	120 °C (measuring accuracy of the internal temperature sensor: ±1 K)		
Relative humidity	≤ 93 % (40 °C/21 d as per EN 60068-2-78); condensation excluded		
Protection EN 60529	Complete encoder, mounted: IP20 ⁹⁾ ; scanning unit: IP40 (read about insulation under Electrical safety in the Interfaces of HEIDENHAIN Encoders brochure)		
Mass	AE scanning unit: ≈ 0.27 kg; TTR scale drum: ≈ 0.17 kg		
ID number	AE ECI4090S scanning unit: ID 1130171-04	TTR EXI4000 scale drum: ID 1130175-02	

Mounting

The scale drum of the rotary encoder is pressed onto the measured shaft's centering collar and fastened. The stator is mounted via an external centering diameter. Use screws with material bonding anti-rotation lock (see Mounting accessories).





For the fault exclusion design for functional safety, the following material properties and conditions for the mating surfaces are assumed. Four possible material combinations are permitted for the customer-side stator and rotor.

	Material				
	Aluminum	Hardenable wrought aluminum alloy	Steel	Unalloyed heat-treated steel	
Tensile strength R _m	≥ 220 N/mm ²		≥ 600 N/mm ²		
Yield strength R _{p0.2} or yield point R _e	-		≥ 400 N/mm ²		
Shear strength Ta	≥ 130 N/mm ²		≥ 390 N/mm ²		
Interface pressure P _G	≥ 250 N/mm ²		≥ 660 N/mm ²		
Modulus of elasticity E (at 20 °C)	70 kN/mm ² to 75 kN/mm ²		200 kN/mm ² to 215 kN/mm ²		
Coefficient of thermal expansion α_{therm} (at 20 °C)	$\leq 25 \cdot 10^{-6} \text{ K}^{-1}$		10 · 10 ⁻⁶ K ⁻¹ to 17 · 10 ⁻⁶ K ⁻¹		
Surface roughness R _Z	≤ 16 µm				
Friction values	Mounting surfaces must be clean and free of grease. Use screws from HEIDENHAIN in their delivery condition.				
Tightening procedure	Use a signal-emitting torque wrench as per DIN EN ISO 6789, with an accuracy of ±6%				
Mounting temperature	15 °C to 35 °C				

Protection from contact (EN 60529)
After encoder installation, all rotating parts must be protected from accidental contact during operation.

5 Product Information ECI 4090 S 11/2024 Product Information ECI 4090 S 11/2024

AE: 10 Hz to 55 Hz, 6.5 mm constant peak to peak; TTR: 10 Hz to 55 Hz, 10 mm constant peak to peak
The encoder must be protected from abrasive and harmful media in the application. Use an appropriate enclosure as needed

Mounting accessories

Screws

Screws are not included in delivery and can be ordered separately.

ECI 4090 S	Screws ¹⁾	Lot size	
Mounting screws for stator and rotor	ISO 4762-M4×25-8.8-MKL	ID 202264-88	60 or 300

¹⁾ With coating for material bonding anti-rotation lock

Please note the information on screws from HEIDENHAIN in the *Encoders for Servo Drives* brochure, under the heading *Screws with material bonding anti-rotation lock* in the chapter *General mechanical information*.

Mounting aid

To avoid damage to the cable, use the mounting aid to connect and disconnect the cable assembly. The pulling force must be applied solely to the connector and not to the wires.


ID 1075573-01

For further mounting information and mounting aids, please refer to the *Encoders* for Servo Drives brochure.



Electrical requirements





Integrated temperature evaluation

These rotary encoders feature an internal temperature sensor integrated into the encoder electronics, as well as an evaluation circuit for an external temperature sensor. In both cases, the respective digitized temperature value is transmitted purely serially via the DRIVE-CLiQ interface. Please bear in mind that neither the temperature measurement nor the transmission of the temperature value is safe in terms of functional safety.

The temperature measured by the internal temperature sensor is higher by a device-specific and application-specific amount than the temperature at measuring point M1 as shown in the dimension drawing.

Upon reaching a trigger threshold for the internal temperature sensor, these rotary encoders issue an "Alarm 135" error message. This threshold may vary depending on the device and is stated in the specifications.

During operation, it is recommended that the temperature be kept adequately below this threshold. Fulfillment of the encoder's intended use requires adherence to the operating temperature at measuring point M1.

Temperature measurement in motors

To protect a motor from overloading, the motor manufacturer usually installs a temperature sensor in close proximity to the motor winding. A PT 1000 temperature sensor or a KTY 84-130 semiconductor sensor, for example, is to be used for this purpose.

For a PT1000, the following values apply with regard to the accuracy of the evaluation circuit:

±6 K at -40 °C to 80 °C ±4 K at 80.1 °C to 160 °C ±6 K at 160.1 °C to 200 °C

For a KTY 84-130 semiconductor sensor, the following values apply with regard to the accuracy of the evaluation circuit: ±6 K at -40 °C to 80 °C ±3 K at 80.1 °C to 160 °C ±6 K at 160.1 °C to 200 °C

The temperature values are transmitted via the DRIVE-CLiQ protocol. The temperature sensor used is adjustable via Parameter 601 in the configuration software (e.g., Starter software) of the

 ${\sf DRIVE\text{-}CLiQ}\ is\ a\ registered\ trademark\ of\ Siemens\ AG.$

6 Product Information ECI 4090 S 11/2024 Product Information ECI 4090 S 11/2024

Online diagnostics and firmware version

For evaluation of the encoder's functionality,
The firmware version can be read via the valuation numbers can be cyclically read from the encoder. These valuation numbers (index 0). The final two digits of the indicate the encoder's current status and displayed value are decisive. can be used to determine its "function reserves." The function reserves are also transmitted via the DRIVE-CLiQ interface and can be displayed in the higher-level control. Further information is available from HEIDENHAIN upon request.

DRIVE-CLiQ parameter "Act_FW_Version"

Electrical connection: pin layout

Pin layout of the ECI

8-pin M12	2 coupling	7	6 5 4	9-pin M23 right-a socket		7 8 9 6 5 4	2	in PCB conn	15 13 11	9 7 5 3 1
		Power	supply			Serial data t	ransmission		Other s	signals ¹⁾
■ M12	8	2	5	1	3	4	7	6	/	1
■ M23	3	7	4	8	5	6	1	2	/	1
E	13	11	14	12	7	8	9	10	5	6
	-	-	0 V	U _P	RXP	RXN	TXP	TXN	T+ ²⁾	T – ²⁾
=	Brown/ Green	Blue	White/ Green	White	Gray	Pink	Violet	Yellow	Brown	Green

Only with output cables inside the motor housing

Cable shield connected to housing; **UP** = Power supply voltage

Note about safety-related applications: use only sufficiently qualified, completely assembled DRIVE-CLiQ cables from HEIDENHAIN or SIEMENS. Do not modify cables or exchange their connectors without first consulting with HEIDENHAIN Traunreut!

Vacant pins or wires must not be used!

9 Product Information ECI 4090S 11/2024 Product Information ECI 4090S 11/2024

²⁾ Connections for an external temperature sensor (depending on the output cable inside the motor housing; see Temperature measurement in motors in the Encoders for Servo Drives brochure)

Electrical connection

Cables

EPG output cables inside the motor housing \varnothing 3.7 mm; $2(2 \times 0.06) + (4 \times 0.06)$ mm ² ; $A_P = 0.06$ mm ² with shield crimping \varnothing 4.3 mm					
With 15-pin PCB connector and 9-pin M23 SpeedTEC angle flange socket (male); wires for temperature sensor1)		ID 1125403-N3 ²⁾ ; length: 0.3 m			
With 15-pin PCB connector and 9-pin M23 SpeedTEC angle flange socket (male)		ID 1125408-N3 ²⁾ ; length: 0.3 m			
With 15-pin PCB connector and M12 coupling (male)	}	ID 1160559-01 ³⁾ ; length: 1 m			

The electromagnetic compatibility of the complete system must be ensured

³⁾ Operating temperature range (conditional): –40 °C to 85 °C

PUR connecting cable \varnothing 6.8 mm; $2(2 \times 0.17 \text{ mm}^2) + (2 \times 0.24 \text{ mm}^2)$; $A_P = 0.24 \text{ mm}^2$					
With 8-pin M12 connector (female) and 8-pin M12 coupling (male)		ID 822504-xx			
With 8-pin M12 connector (female) and RJ45 Siemens connector (IP67)		ID 1094652-xx			
With 8-pin M12 connector (female) and RJ45 Siemens connector (IP20)	<u></u>	ID 1093042-xx			
With M23 SpeedTEC connector (female) and RJ45 Siemens connector (IP20)		ID 1121546-xx			
With 8-pin M23 SpeedTEC connector (female) and 8-pin M12 coupling (male)	<u></u>	ID 1121536-xx			

Ap: Cross section of power supply lines

Output cables may require strain relief. Always provide strain relief for cable lengths > 0.5 m.

SpeedTEC is a registered trademark of Intercontec Pfeiffer Industriesteckverbindungen GmbH. DRIVE-CLiQ is a registered trademark of SIEMENS AG.

HEIDENHAIN

DR. JOHANNES HEIDENHAIN GmbH Dr.-Johannes-Heidenhain-Straße 5 83301 Traunreut, Germany

2 +49 8669 31-0 FAX +49 8669 32-5061 info@heidenhain.de

www.heidenhain.com

This Product Information document supersedes all previous editions, which thereby become invalid. The basis for ordering from HEIDENHAIN is always the Product Information document edition valid when the order is placed.



Comply with the requirements described in the following documents to ensure correct and intended operation:

• Brochure: Encoders for Servo Drives

ID 208922-xx

• Brochure: Cables and Connectors

ID 1206103-xx

• Mounting instructions: AE ECI4090S

ID 1184567-xx

• Mounting instructions: TTR EXI4000

ID 1147618-xx

• Brochure: Interfaces of HEIDENHAIN Encoders

ID 1078628-xx

²⁾ Operating temperature range (conditional): –20 °C to 120 °C